



Door closer 7505 Compact

Information

You have just acquired a high quality AXA product. The instructions below must be followed closely in order to effectively install and operate this product.

Application

For doors: maximum 40 kg or 850 mm wide.

Installation tools (recommended)

Tape measure, (battery) drill, screwdriver, drill Ø 3,5, bradawl/pencil.

Installation manual



Do not turn the shaft more than 180° before installing the door closer's hold-open function, otherwise the door closer will be damaged.

- 1 Determine the direction in which the door opens and use the information at the top right of this page to determine where to install the door closer (door or frame).

Mounting on the pull side of the door

- 2A Mark the holes (pre-drill Ø 3.5 mm) in the door and frame, then install the door closer on the door. (figure **A**).

Mounting on the push side of the frame

- 2B Mark the holes (pre-drill Ø 3.5 mm) in the door and frame, then attach (5.0 x 30 mm, 4 pcs.) the door closer to the frame. (figure **B**).

- 3 Place the main arm on the door closer shaft using the supplied bolt and washer. (figure **A** or **B**).


- 4 When the door closer housing is mounted, the valves must face the hinge side (figure **C**).

- 5 Determine whether a slightly higher or slightly lower closing power is required. (figuur **D**). Attach the forearm armrest to the window frame (5.0 x 25 mm, 2 pcs.).

- 6 Adjust the length of the lower arm so that it is at a right angle (90°) to the closed door, then tighten the lock nut (figure **E**).

- 7 Place the cap on and turn it slightly.

- 8 Set the desired closing speed (1) and end stroke (2) (figure **C**).



Do not unscrew the valve from the holder, as this may cause oil leakage and adjustment problems.

An average door closing time from 90° to 0° is between 4 and 6 seconds. For elderly people and children, the closing time may be longer.

Recommended fasteners: hex bolt M6x15, screws 5,0 x 30 (4x), round-head screws 5,0 x 25 (2x), round-head metal screws M5 x 25 (2x), metal screws M5 x 17, cap

